

TECHNICAL DATASHEET



WWW.CLEAN-AIR.CZ

CleanAIR® MedicAER® Powered air purifying respirator



Description

The battery-powered air purifying respirator (PAPR), the breathing protective device for increasing comfort and safety when combined with approved headtops.

For more information go to <http://www.medic-aer.com/>

Application

In default MedicAER® provides protection against particulates, but is also capable to provide protection against wide range of contaminants when used with combined filters.

DA-069_-_51M000FC_-_MedicAER_-_EN

TECHNICAL DATASHEET

CleanAIR® MedicAER® Powered air purifying respirator



Technical specification

Product code	51 M0 00FC		
Flow rate	Airflow [lpm]	Mode	Filter category
	120 / 140 / 160	Mask EN 12942	Particle
	120 / 140 / 160		Light combined (class 1)
	120 / 140 / 160		Heavy combined (class 2)
	120 / 140 / 160		Heavy combined (class 3)
	160 / 185 / 210 / 235	Hood EN 12941	Particle
	160 / 185 / 210		Light combined (class 1)
	160		Heavy combined (class 2)
160	Heavy combined (class 3)		
Battery	Standard battery	Heavy duty battery	
Voltage	14,4 V	14,4 V	
Capacity	2,6 Ah	5,2 Ah	
Charging time	< 3 hours	< 6 hours	
Operation time*	< 10 hour*	< 20 hours*	
Battery lifespan	up to 500 charging cycles	up to 500 charging cycles	
Battery charger	Microprocessor controlled, fully automatic Input: 100 - 240 V (50/60 Hz) Output: 18 V (max. 1 500 mA) Available plugs: EUR, UK and AUS		
Weight	1000 g (incl. standard battery, excl. filters)		
Dimensions	235 mm / 126 mm / 65 mm (with standard battery)		
Noisiness	< 70 dB		
Materials	Unit: high performance polyamide Belt: textile part - polyester/nylon/rubber foam plastic part - polyamide		
Motor	Ball-bearing brushless motor		
Input / Output (threads)	Filter thread - RD40x1/7" - 2x Airflow output thread - CA40x1/7" - 1x		
Belt - waist size:	Comfort padded belt - up to 1 500 mm		
Standard	EN 12941	EN 12942	
Protection class / NPF***	TH3 / 500	TM3 / 2000	
Ingress protection	IP64:	When switched ON (without any further requirements)	
	IP65:	When switched ON (set of spark arresters and pre-filter holders - 50 01 12)	
	IP68:	When switched OFF (with plugged inputs and output - 51 00 46)	
Display	TFT display (262k colours, 160x160 px) (showing actual working mode, airflow, filter condition and battery status)		
Storage conditions	- 10°C to + 55°C, humidity 20 - 95 % Rh		
Operating conditions	0°C to + 60°C, humidity 20 - 95 % Rh		

* with new P3 filters and fully charged battery / ** depends on used headtop

Disclaimer Notice

All the information contained herein is believed to be accurate and is subject to change without notice. Users should independently evaluate the suitability of each product for their own applications. CleanAIR® products are not designed for, and may not be used in, all applications.

TECHNICAL DATASHEET

CleanAIR® MedicAER® Powered air purifying respirator



Product sets / variations

51 MO 00FC	Powered air purifying respirator CleanAIR® MedicAER, QuickLOCK® light flexi hose, exchangeable battery, charger (EURO - plug), comfort padded belt and flow indicator
51 MO 00FD	Powered air purifying respirator CleanAIR® MedicAER, QuickLOCK® light flexi hose, exchangeable battery, charger (EURO - plug), PVC belt and flow indicator

* Add U or AUS to the end of product code for ordering charger with UK or AUS plug

Spare parts and accessories

51 00 10	Standard battery Li-Ion 14,4 V / 2,6 Ah
51 00 20	Heavy Duty battery Li-Ion 14,4 V / 5,2 Ah
71 00 92	Comfort padded belt
72 00 92	Comfort leather belt
51 00 51	Decontaminable belt PVC - 2F/3F
51 00 52	Decontaminable harness PVC - 2F
52 00 44.1	Comfort padded harness
71 00 60	Light flexi hose QuickLOCK™ - CA40x1/7"
71 00 86	Rubber hose QuickLOCK™ - CA40x1/7"
71 00 62F	Hose cover flameproof
70 00 62C	Hose cover chemical resistant
51 00 30EUR	Charger for CleanAIR® Chemical 2F (EURO - plug)
51 00 30UK	Charger for CleanAIR® Chemical 2F (UK - plug)
51 00 30AUS	Charger for CleanAIR® Chemical 2F (AUS - plug)
51 00 46	Set of plugs (2x external thread, 1x internal thread) for decontamination of unit 2F
52 01 01	TFT display protective foil

Technical features

Warning system - visual and audible warning for low airflow and low battery charge..

Flow control system - maintains level of airflow constant regardless filter clogging or battery charge.

Automatic closing system - reduces the risk of unwanted contamination of the unit while the filters are being changed

Allows immersion disinfection - with input and output threads plugs on (Sodium hypochloride or Persteril).

Stainless steel battery connectors - prolong lifetime if decontaminated frequently.

LED display - LED display visualises airflow, filter clogging and battery charge.

Disclaimer Notice

All the information contained herein is believed to be accurate and is subject to change without notice. Users should independently evaluate the suitability of each product for their own applications. CleanAIR® products are not designed for, and may not be used in, all applications.

TECHNICAL DATASHEET

CleanAIR® MedicAER® Powered air purifying respirator



Compatible filters

Product code:	Product name	P-white	A-brown	AX-brown	B-grey	E-yellow	K-green	Hg-red	Ozone (10 ppm)	EN 14387	EN 143	EN 12941	EN 12942	EN 148-1 (RD40x17")	Note:
Combined filters, thread RD40*1/7"															
50 03 57	A1P3	✓	✓									✓	✓	✓	-
50 01 57	A2P3	✓	✓						✓			✓	✓	✓	-
50 01 70	A3AXP3	✓	✓	✓								✓	✓		-
50 01 62	B2P3	✓			✓				✓	✓		✓	✓	✓	-
50 01 60	K2P3	✓				✓			✓	✓		✓	✓	✓	-
50 01 67	A2B2P3	✓	✓		✓				✓	✓		✓	✓	✓	-
50 01 64	A2B2E2P3	✓	✓		✓	✓			✓	✓		✓	✓	✓	-
50 03 64	A1B1E1P3	✓	✓		✓	✓						✓	✓	✓	-
50 01 68	A2B2E2K2P3	✓	✓		✓	✓	✓		✓	✓		✓	✓	✓	-
50 01 65X	NBC - A2B2E2K2P3	✓	✓		✓	✓	✓		✓			✓	✓	✓	NBC filter
50 01 66	A2B2E2K2HgP3	✓	✓		✓	✓	✓	✓	✓	✓		✓	✓	✓	max. 50 hours
50 02 57	A2P - ZERO	✓	✓						✓			✓	✓	✓	two-thread filter
50 02 66	A2B2E2K2HgP - ZERO	✓	✓		✓	✓	✓	✓	✓	✓		✓	✓	✓	two-thread filter
50 02 68	A2B2E2K2P - ZERO	✓	✓		✓	✓	✓		✓	✓		✓	✓	✓	two-thread filter
Particle filters, thread RD40*1/7"															
50 00 48	P3	✓									✓	✓	✓	✓	-
50 02 49	ZERO	✓									✓	✓	✓	✓	two-thread filter
50 40 48	P3 lite	✓									✓	✓	✓	✓	-
50 42 49	ZERO lite	✓									✓	✓	✓	✓	two-thread filter

Disclaimer Notice

All the information contained herein is believed to be accurate and is subject to change without notice. Users should independently evaluate the suitability of each product for their own applications. CleanAIR® products are not designed for, and may not be used in, all applications.

TECHNICAL DATASHEET

CleanAIR® MedicAER® Powered air purifying respirator



Compatible headtops

72 01 01	Short hood CA-1 Lite	TH3
72 02 01	Long hood CA-1 Lite	TH3
72 01 02B	Short protective hood CA-1, blue	TH3
72 01 02	Short protective hood CA-1, orange	TH3
72 01 12	Short protective hood CA-1+, orange	TH3
72 01 12B	Short protective hood CA-1+, blue	TH3
72 02 02B	Long protective hood CA-2, blue	TH3
72 02 02	Long protective hood CA-2, orange	TH3
72 10 02	Chem-proof protective hood CA-10	TH3
72 10 02G	Chem-proof protective hood CA-10, grey	TH3
72 03 00.01	Protective face shield UniMask, grey	TH3
72 03 00.02	Protective face shield UniMask, blue	TH3
72 03 00.03	Protective face shield UniMask, orange	TH3
72 03 00.04	Protective face shield UniMask, red	TH3
72 03 00.08	Protective face shield UniMask, neoprene	TH3
71 03 01	Grinding shield CA-3 (acetate visor)	TH2
70 05 00	Half mask CA-5 Eurmask DIN	TM2
71 06 00	Full face mask GX02, size [S, M, L]	TM3
72 06 00	Full face mask CF02, size [M, L]	TM3

Disclaimer Notice

All the information contained herein is believed to be accurate and is subject to change without notice. Users should independently evaluate the suitability of each product for their own applications. CleanAIR® products are not designed for, and may not be used in, all applications.